



Recharge Pulse Wave

www.ReChargePulseWave.com

Dr. Larry Basch, D.C., CCSP, CCEP, ICSC LBASCHDC@gmail.com Ph: 858-945-8118
EIN # 26-1657557 CA Resale Permit # 22-4191872 DUNS# 133874680 Cage # 3GN74



MODEL 1.2 COMBO ReCharge PEMF units are the ONLY high power PEMF manufacturer to be safety tested having UL / CL certification, manufactured in an ISO 13485 Certified Facility, is conducting University research, and is made in the USA. And this is the only brand approved for sale to local, state and federal agencies, Department of Defense, US Navy / Marine Corps.

High Intensity PEMF creates an electric field within a magnetic coil and requires the use of a capacitor to store energy, which takes some time to build up. It will then discharge that stored energy in a microsecond. The frequency of discharge is related to the power setting machines. If you increase the power, the frequency is decreased due to the capacitor limits.

Other low power units (often called "Hummers") use a high frequency oscillator with extremely low power output. The power output is so low; patients do not feel these fast oscillations passing through the body. This results in very long treatment times with little noticeable benefits. With our High Power PEMF, you feel it right away, so there is no doubt its working, you feel the pulse immediately deep within the body. This allows for the shortest treatment times & deeper tissue penetration.

ReCharge PEMF is the **ONLY Brand of PEMF** using Dual Coils delivering **Dual Pulsing** offering the proven benefits of both Low Power PEMF & High-Power PEMF running simultaneously so a second 10Hz baseline low power pulse is always running in addition to the higher intensity PEMF which you can select the power setting. So you get two different machines with two different pulses running simultaneously or (**DUAL PULSE FREQUENCY**) in one medical grade machine.

* (We offer three different Dual Pulse High Power units. This is the medium priced & medium power output of our high-power units, meaning slightly longer treatment times and slightly less depth of penetration as the highest power units.)

The new digital **Model 1** is a small compact, portable unit with a lower spectrum of the high power Dual Pulsing PEMF. It is still high-intensity impulse system and is suitable for use both in-home or in a clinical setting. This unit has five levels of adjustable power output with an estimate 5000 gauss max and a 30 & 60 minute timer.

Model #1.2 COMBO Compact PEMF



Low-Medium Power

Includes Two Attachments: (shown 1 Small Mat (18" x 24") & PEMF Helmet for Brain Concussion / Alzheimer's / Anti Aging)



ReCharge Package with 2 Attachments Pad & Helmet



ReCharge MODEL 1.2 COMBO Package with 2 Attachments

Note: With Model 1.2, you can choose TWO Attachments

Other Attachments sold separately: Large Loop, Pelvic Floor Pad, Butterfly Double Loops

More Detailed PEMF info at: www.ReChargePulseWave.com LBASCHDC@gmail.com Ph: 858-945-8118

Stearns Bank Ellen Boquist 800-247-1922 Ext. 3199 cell: 320-248-7116 EllenB@stearnsbank.com www.stearnsbank.com
NCMIC Scott Fuller 877-770-7244, ext. 4685 cell 515-313-4685 sfuller@ncmic.com www.ncmic.com